Mobile thermofixing device

MÜTHERM 2/450

for the thermofixing of light and medium-weight narrow fabrics from both sides



MÜTHERM 2/450

Concept

This mobile dry thermosetting device for thermosetting and shrinkage effects offers maximum flexibility of application. It can be fitted before or behind the individual production machines for targeted use in continuous operation, or employed as a free-standing unit for independent operation. An separate downstream winder is recommended (not included in delivery volume).

The infeed roller and outlet roller are driven by separate motors. Thus the speeds can be set individually. The fine adjustment is done by rotary potentiometers.

The temperature of the two rollers can be controlled individually. Both rollers have a hot and cold zone. In order to prevent heat damage, during each standstill the rollers automatically turn their cold zone to the fabric.

MÜTHERM-devices make your products even more valuable and due to their compact design can be easily fitted into the production process.


For permanent use our looms and knitting machines can also be fitted with integrated thermosetting units.



Separately controlled motors for infeed and outlet roller



Operation panel (also available with encoder)



MÜTHERM 2/450: free-standing, mobile unit and fitted unit

Technical Data

Connection	3 x 400 V – 50/60 Hz		
Heat output	1,2 kW per roller		
Temperature	115 - 240°C, separate, infinite		
adjustment for each roller			
Warm-up time 5 – 15 min, depending on the			
working temperature			
Working width	450 mm		

Fascination of Ribbons and Narrow Fabrics

Dimension

Width	870 mm
Height	1330 mm
Depth	1000 mm

Copyright © 1987 by Jakob Müller AG Frick 5070 Frick Switzerland

Printed in Switzerland. All rights reserved.

No part of this publication may be reproduced by any means, nor translated, nor transmitted into a machine language without the written permission of the publisher.

This leaflet contains photos and technical data for information only, without contractual engagement.

Rep.:



Jakob Müller AG Frick 5070 Frick Switzerland Tel +41 62 8655 111 Fax +41 62 8655 777 www.mueller-frick.com

Innovation in Machinery

